

DATA SHEET

TK860V001 Splitter cable

Freelance hardware selector

TK860V001 Splitter cable (CAB 109). Splitter cable Version 6 panel. Y-split cable to utilize more than two COM ports on Version 6 panels. Length 0.1 m. DB-9 male and DB-9 female connection. Not possible to use with PP887S.

**General info**

Article number	3BSE069476R1
Dimension WxHxD (mm)	76x190x100 mm
Net weight (kg)	0.11 kg
Operating temperature	-30 °C to +70 °C

Environment and certification

Relative operating humidity	5 % – 95 % non-condensed
Storage temperature	-40 °C to +80 °C
CE-marking	CE
RoHS compliance	EU RoHS, UAE RoHS, CN RoHS
WEEE compliance	DIRECTIVE/2012/19/EU

solutions.abb/freelance
solutions.abb/controlsystems

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2026 ABB All rights reserved