

DATA SHEET

CB802 Profibus DP Interface

Freelance hardware selector



CB802 Profibus DP Communication Interface. PROFIBUS DP slave expansion module for Panel 800 Version 6 panels. Not possible to use for PP880R, PP885H, PP885M, PP885R, PP886R, PP886H, PP887H and PP887S.

General info		
Article number	3BSE069285R1	
Operating temperature	-30 °C to +70 °C	
Detailed data		
Interaction type	Communication speed: 12000 kbit/s	
Environment and certification		
Relative operating humidity	5 % – 95 % non-condensed	
Storage temperature	-40 °C to +80 °C	
CE-marking	CE	
RoHS compliance	DIRECTIVE/2011/65/EU	
WEEE compliance	DIRECTIVE/2012/19/EU	
Dimensions		
Height	35 mm	
Width	130 mm	
Weight	0.18 kg	



solutions.abb/freelance solutions.abb/controlsystems

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved