

# CI 930F

## Freelance hardware selector

PROFIBUS Master module for DP-V0/V1, 12 MBit/s. Supports PROFIBUS line redundancy. Two D-Sub terminals (9-pole), one each for line A/B. Software version 2013 or higher is mandatory. Use with AC 900F controllers.



### Features and benefits

- Supports built-in line redundancy
- Supports PROFIBUS line redundancy
- Support hot plug
- IP20 protection

General info	
Article number	3BDH001010R0002
Communication protocol	Communication Interface, PROFIBUS DP Master
Life cycle status	Active
Transmission speed	9.6 kBit/s to 12 MBit/s
Line redundancy	Yes
Hot Swap	Yes

Detailed data	
Connector	Two D-Sub terminals (9-pole)
24 V consumption typ.	80 mA, via 24 V terminal of CPU module
Power dissipation	1.8 W

---

**Environment and certification**

---

Temperature, Operating	-20°C ... +70°C
Temperature, Storage	-40 ... + 85°C
Altitude	< 2000 m
Corrosion protection	G3 compliant acc. ISA 71.04
Relative humidity	max. 95%, non-condensing
Protection class	IP20
Emission & Immunity	EN 61000-6-4, EN 61000-6-2
CE-marking	Yes
Electrical Safety	IEC/EN 61010-1, IEC/EN 61010-2-201
Hazardous location	cULus Class 1 Div 2
RoHS compliance	Directive 2011/65/EU, (EU) 2015/863
WEEE compliance	Directive 2012/19/EU

---

---

**Dimensions**

---

Width	28 mm
Height	152 mm
Depth	85 mm
Weight	115 g

---

—  
**[solutions.abb/freelance](https://solutions.abb/freelance)**  
**[solutions.abb/controlsystems](https://solutions.abb/controlsystems)**

—  
We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved