

CI 773F

Freelance hardware selector



A PROFIBUS Master communication interface for communication with the PROFIBUS DP fieldbus devices or remote I/Os. PROFIBUS PA support via separate PA/DP coupler. DP-V0/V1, 12 MBit/s. 1 x D-Sub terminal, 9-pole. Line redundancy via external RLM02. Software version 2013 SP1 or higher is mandatory. Use with AC 700F or AC 900F

Features and benefits

- Supports controller redundancy
- PROFIBUS DP master
- IP20 protection

General info	
Article number	3BDH000395R0001
Communication protocol	Communication Interface, PROFIBUS DP Master
Life cycle status	Active
Transmission speed	9.6 kBit/s to 12 MBit/s
Line redundancy	No
Hot Swap	Yes

Detailed data	
Connector	D-Sub terminal, 9-pole
24 V consumption typ.	80 mA, via 24 V terminal of CPU module
Power dissipation	1.6 W

Environment and certification

Temperature, Operating	-20°C ... +70°C
Temperature, Storage	-40 ... + 85°C
Altitude	< 2000 m
Corrosion protection	G3 compliant acc. ISA 71.04
Relative humidity	max. 95%, non-condensing
Protection class	IP20
Emission & Immunity	EN 61000-6-4, EN 61000-6-2
CE- marking	Yes
Electrical Safety	IEC/EN 61010-1, IEC/EN 61010-2-201
Hazardous location	cULus Class 1 Div 2
RoHS compliance	Directive 2011/65/EU, (EU) 2015/863
WEEE compliance	Directive 2012/19/EU

Dimensions

Width	28 mm
Height	135 mm
Depth	75 mm
Weight	96 g

—
solutions.abb/freelance
solutions.abb/controlsystems

—
We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2026 ABB All rights reserved