

CI840A

Freelance hardware selector



S800 I/O is a comprehensive, distributed and modular process I/O system that communicates with parent controllers and PLCs over industry-standard field buses. The CI840 Fieldbus Communication Interface (FCI) module is a configurable communication interface that performs operations such as signal processing, gathering of various supervision information, OSP handling, Hot Configuration In Run, HART pass-through and configuration of I/O modules. CI840 is designed for redundant applications. The FCI connects to the controller by way of the PROFIBUS-DPV1 fieldbus. Module termination units to use, TU846 with redundant I/O and TU847 with non-redundant I/O.

Features and benefits

- PROFIBUS DP PROFIBUS-DPV1 fieldbus interface.
- Supervisory functions of I/O ModuleBus
- Isolated power supply to I/O modules
- OSP handling and configuration
- Input power fused
- Hot Configuration In Run
- HART pass-through

General info	
Article number	3BSE041882R1
Communication protocol	PROFIBUS DP-V1
Master or slave	Slave
Line redundancy	Yes
Module redundancy	Yes
Hot Swap	Yes
Used together with HI Controller	Yes

Detailed data	
24 V consumption typ.	190 mA

Environment and certification	
CE- marking	Yes
Electrical Safety	EN 61010-1, UL 61010-1, EN 61010-2-201, UL 61010-2-201
Hazardous location	C1 Div 2 cULus, C1 Zone 2 cULus, ATEX Zone 2
Marine certificates	ABS, BV ,DNV-GL, LR
Temperature, Operating	0 to +55 °C (+32 to +131 °F), approvals are issued for +5 to +55 °C
Temperature, Storage	-40 to +70 °C (-40 to +158 °F)
Pollution degree	Degree 2, IEC 60664-1
Corrosion protection	ISA-S71.04: G3
Relative humidity	5 to 95 %, non-condensing
Max ambient temperature	55 °C (131 °F), for vertical mounting 40 °C (104 °F)
Protection class	IP20 according to EN60529, IEC 529
RoHS compliance	DIRECTIVE/2011/65/EU (EN 50581:2012)
WEEE compliance	DIRECTIVE/2012/19/EU

Dimensions	
Width	54 mm (2.13 in.)
Height	119 mm (4.69 in.)
Depth	96 mm (3.78 in.)
Weight	0.2 kg (0.44 lbs.)

**solutions.abb/freelance
solutions.abb/controlsystems**

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved