

TU 715F

Freelance hardware selector



The I/O Terminal Units TU 715F (screw type terminal) and TU 716F (spring type terminal) are used as a socket for the I/O module, which exclusively incorporates inputs and outputs for 24V DC digital or analog signals.

The I/O modules (I/O expansion modules) are placed on the I/O Terminal Unit and locked into place using two mechanical locks. To loosen this connection a screwdriver should be inserted in the recess provided and the Terminal Units are carefully pulled away. All electrical connections are made through the Terminal Unit, which allows the removal and replacement of the I/O units without disturbing the wiring at the terminal unit.

General info

Article number	3BDH000378R0001
Signal specification	I/O terminal unit
Mechanics	S700
Design	Screw type terminals, 1/2 wire.

Detailed data

Load current	10 A
Common mode voltage input	24 VDC
Supported wire size	0.08 ... 2.5 mm ²

Environment and certification

CE mark	Yes
Electrical safety	EN 50178, IEC 61131-2, UL 61010-1, UL 61010-2-201
Hazardous Location	cULus Class 1 Div 2
Protection rating	IP20
RoHS compliance	Directive 2011/65/EU
WEEE compliance	DIRECTIVE/2012/19/EU

Dimensions	
Width	68 mm
Depth	30 mm
Height	135 mm
Weight	0.19 kg

—
solutions.abb/freelance
solutions.abb/controlsystems

—
We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved