

TU921N RTU (TU16R)

Freelance hardware selector



The remote S900 I/O system can be installed in non-hazardous areas or directly in Zone 1 or Zone 2 hazardous area depending on the selected system variant. S900 I/O communicates with the control system level using the PROFIBUS DP standard. The I/O system can be installed directly in the field, therefore the costs for marshalling and wiring are reduced.

The system is sturdy, error-tolerant and easy to service. Integrated disconnection mechanisms allow replacement during operation, meaning that there is no need to interrupt the primary voltage in order to exchange the power supply units.

S900 I/O type N. For installation in safe (= non-hazardous) area.

TU921N Redundant Termination Unit (TU16R), for 16 I/O-modules, redundant communication and power (Delivery includes CD910).

Features and benefits

- For installation in safe areas (non-hazardous)
- Redundancy (Power and Communication)
- Hot Configuration in Run
- Hot Swap functionality
- Extended Diagnostic
- Excellent configuration and diagnostics via FDT/DTM
- G3 – coating for all components
- Simplified maintenance with auto-diagnostics
- Mounting in safe area possible
- Termination unit for up to 16 I/O modules
- Prepared for redundant system power and communication
- Up to 4 terminals per channel
- Pre-selection of fieldbus address
- Prepared for certified field housing
- Mounting only in safe area possible

General info

Article number	3KDE175113L9210
Signal type	Redundant termination unit
SOE	N/A
Redundancy	No
Intrinsic safety	Yes
Mechanics	S900

Detailed data

Supported wire size	0,5 ... 2,5 mm ²
---------------------	-----------------------------

Environment and certification

CE mark	Yes
Corrosive atmosphere ISA-S71.04	G3
Climatic operating conditions	Relative humidity max. 93 % +/- 3 % at 40°C
Max ambient temperature	-20 °C...+60 °C
RoHS compliance	DIRECTIVE/2011/65/EU (EN 50581:2012)
WEEE compliance	DIRECTIVE/2012/19/EU
WEEE category	Small Equipment (No External Dimension More Than 50 cm)

Dimensions

Width	498 mm (19.6 in.)
Depth	147 mm (5.8 in.)
Height	274 mm (10.8 in.)
Weight	3.7 kg (8.15 lbs.)

—
solutions.abb/freelance
solutions.abb/controlsystems

—
We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2024 ABB All rights reserved