

DATA SHEET

DO815

Freelance hardware selector



The DO815 is a 8 channel 24 V digital output module for the S800 I/O. The output voltage range is 10 to 30 V and the maximum continuous output current is 2 A @ 24 V. The outputs are protected against short circuits, and over load. The outputs are divided into two individually isolated groups with four output channels in each group. Each output channel consists of a short circuit and over load protected high side driver with open load detection (on active signal), EMC protection components, inductive load suppression, output status indication LEDs and optical isolation barrier.

Features and benefits

- 8 channels for 24 V d.c. current sourcing outputs
- 2 isolated groups of 4 channels with under voltage detection
- OSP sets outputs to predetermined state upon communication error
- Output status indicators and a channel wise error flag
- Short-circuit protection to ground and positive supply
- Over load protection
- Open load and short-circuit detection
- Two output fault operation modes: Automatic reset mode and Fault latching mode
- Inductive load driving capability
- Filament lamp load up to 10W

General info		
Article number	3BSE013258R1	
Туре	Digital Output	
Signal specification	24 V d.c. (10 - 32 V d.c.), 2A	
Number of channels	8	
Signal type	High side driver, current limiting	
HART	No	
SOE	No	
Redundancy	No	
High integrity	No	
Intrinsic safety	No	
Mechanics	S800	

Detailed data		
Isolation	Groupwise isolated from ground	
Output load	< 0.25 Ω	
Current limiting	Short circuit proof current limited output	
Maximum field cable length	600 meters (656 yards)	
Event recording accuracy	-0 ms / +1.3 ms	
Rated insulation voltage	50 V	
Dielectric test voltage	500 V a.c.	
Power dissipation	Typ. 4 W	
Current consumption +5 V Modulebus	Typ. 120 mA, Max. 150 mA	
Current consumption +24 V Modulebus	0	
Current consumption +24 V external	0	

Diagnostics		
Front LED's	F(ault), R(un), W(arning), O(SP), Channel 1-8 Status, Channel 1-8 Fault	
Supervision	Short circuit, over load, under voltage and open load	
Status indication of supervision	Module Error, Module Warning, Channel error	

Environment and certification		
CE mark	Yes	
Electrical safety	EN 61010-1, UL 61010-1, EN 61010-2-201, UL 61010-2-201	
Hazardous Location	C1 Div 2 cULus, C1 Zone 2 cULus, ATEX Zone 2	
Marine certification	ABS, BV, DNV, LR	
Temperature, Operating	0 to +55 °C (+32 to +131 °F), approvals are issued for +5 to +55 °C	
Temperature, Storage	-40 to +70 °C (-40 to +158 °F)	
Pollution degree	Degree 2, IEC 60664-1	
Corrosion protection	ISA-S71.04: G3	
Relative humidity	5 to 95 %, non-condensing	
Max ambient temperature	55 °C (131 °F), for vertical mounting in compact MTU 40 °C (104 °F)	
Protection class	IP20 according to IEC 60529	
Mechanical operating conditions	IEC/EN 61131-2	
EMC	EN 61000-6-4, EN 61000-6-2	
Overvoltage categories	IEC/EN 60664-1, EN 50178	
Equipment class	Class I according to IEC 61140; (earth protected)	
RoHS compliance	DIRECTIVE/2011/65/EN (EN 50581:2012)	
WEEE compliance	DIRECTIVE/2012/19/EU	

Compatibility	
Use with MTU	TU810, TU812, TU814, TU830
Keying code	AA

Dimensions		
Width	45 mm (1.77")	
Depth	102 mm (4.01"), 111 mm (4.37") including connector	
Height	119 mm (4.7")	
Weight	0.2 kg (0.44 lbs.)	

Related products



TU814V1



solutions.abb/freelance solutions.abb/controlsystems

We reserve the right to make technical changes to the products or modify the contents of this document without prior notice. With regard to purchase orders, the agreed particulars shall prevail. ABB does not assume any responsibility for any errors or incomplete information in this document.

We reserve all rights to this document and the items and images it contains. The reproduction, disclosure to third parties or the use of the content of this document – including parts thereof – are prohibited without ABB's prior written permission.

Copyright© 2025 ABB All rights reserved